



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LEMWR2 Pathlinx Remote Head Wet Location 2-Head *Cooper Lighting Solutions*

| | |
|------------------|---------------------------------|
| Catalog Number | LEMWR2 |
| Manufacturer | Cooper Lighting Solutions |
| Description | Led Remote 2 Head, Wet Location |
| Weight per unit | 0.9300 (lbs/each) |
| Product Category | Emergency Lighting |

Features

| | |
|-----------------|---|
| amperage rating | 4m A |
| Lamp Type | INCANDESCENT LANDSCAPE LIGHT FIXTURE, ECLIPSE TYPE; ALUMINUM MATERIAL; 4.5 INCH W X 18.5 INCH H SIZE; TEXTURED ARCHITECTURAL BRONZE FINISH; UL (CANADA AND US), CSA, ETL (US) APPROVAL; 8 INCH IN-GROUND STAKE, 18 INCH STEM MOUNTING |
| Voltage Rating | 120/277 VAC |
| Wattage | 1 PH |

Dimensions and Weight

| | |
|------|---|
| Size | 5.375 IN Length 5.375 IN Width 3.75 IN Height |
|------|---|

Descriptions

| | |
|------------------|--|
| Description | PATHLINX REMOTE HEAD WET LOCATION 2-HEAD |
| Long Description | LED Remote 2 head, wet location |
| Product Type | Led Remote, 2 HD, Wet |
| Special Features | LED Emergency Light |

Manufacturer Information

| | |
|---------------------------|-----------------|
| Brand | Eaton Lighting |
| GTIN | 00080083637386 |
| Manufacturers Part Number | LEMWR2 |
| sub brand | PathLinx Remote |
| UPC | 080083637386 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---------------------------|
| Category Description | Emergency & Exit Lighting |
| Type | Emergency |

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Package | 24 |
| Weight Per each | 0.93 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|-------------------|--|
| Application | lighting |
| Mounting | Surface Mount |
| standard | UL924 Listed; NFPA 101 Compliant |