



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LFV148Q Highland Vinyl Ins Locking Fork Term, 16-14awg *Minnesota Mining (3M)*

Catalog Number	LFV148Q
Manufacturer	Minnesota Mining (3M)
Description	Locking Fork, #16 Awg Conductor Size, #14 Awg Conductor Size, Insulated, Vinyl Insulation Material, Blue Insulation Color, -40 °F Operating Temperature, +221 °F Operating Temperature, 0.07 LB
Weight per unit	0.0070 (lbs/each)
Product Category	Small Terminals & Connectors

Descriptions

Description	HIGHLAND VINYL INS LOCKING FORK TERM, 16-14AWG
extra long description	3M 7000133666 3M™ Highland™ Vinyl I
Features	3M™ Highland™ Locking Fork Terminal is color-coded for quick and easy identification of the wire size required. It has a butted-seam barrel that is covered by a funnel-designed, rigid-molded, polyvinyl chloride sleeve to guide the wire into position while providing electrical contacts and mechanical stress relief at the point of insulation. The abrasion-resistant, flared, vinyl-sleeve insulation ensures easy crimping. UL Listed, CSA Certified and RoHS 2011/65/EU Compliant.

Manufacturer Information

Brand	Scotchlok
GTIN	00051128600191
Manufacturers Part Number	LFV148Q
UPC	051128600191

Taxonomies, Classifications, and Categories

Category Description	TERMINALS
Type	LOCKING

Packaging

Carton	10
Weight Per each	0.007

Uses, Certifications, and Standards

standard	UL and CSA
----------	------------