

Eaton LGE3350FAG

Catalog Number: LGE3350FAG

Eaton Series G molded case circuit breaker, LG-frame, LG, Fixed thermal, adjustable magnetic trip, Three-pole, 350 A, 65 kAIC at 240 Vac, 35 kAIC at 480 Vac, 18 kAIC at 600 Vac, Line and load, Metric, 50/60 Hz, 80% rated



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Series G complete molded case circuit breaker	LGE3350FAG
	UPC
	782116142392
Product Length/Depth	Product Height
4.09 in	5.48 in
Product Width	Product Weight
5.48 in	14.5 lb
Warranty	Compliances
Eaton Selling Policy 25-000, one (1) year CE Marked from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	Certifications
	IEC Rated
	UL Listed
	CSA Certified

Catalog Notes

LG breaker is HACR rated

defaultTaxonomyAttributeLabel

Type

Complete breaker

Amperage Rating

350 A

Trip Type

Fixed thermal, adjustable magnetic

Circuit breaker type

LG

Circuit breaker frame type

Complete breaker

Rating

80% rated

Series

Series G

Terminals

Line and load

Frame

LG

Frequency rating

50 to 60 Hz

Mounting hardware

Metric

Interrupt rating

35 kAIC at 480 Vac

18 kAIC at 600 Vac

65 kAIC at 240 Vac

Number of poles

Three-pole

Resources

Application notes

[Application of Tap Rules to Molded Case Breaker Terminals](#)

[Application of Multi-Wire Terminals for Molded Case Circuit Breakers](#)

Brochures

[Multi-wire lugs product aid](#)

[Series G MCCB quick selector](#)

[Comprehensive circuit protection for control panel applications](#)

[High performance operating handles for Series G circuit breakers product aid](#)

[Molded case circuit breakers providing higher levels of selective coordination product aid](#)

[StrandAble terminals product aid](#)

[Power metering and monitoring with Modbus RTU product aid](#)

[Circuit breaker motor operators product aid](#)

[Plug-in adapters for molded case circuit breakers product aid](#)

[Motor protection circuit breakers product aid](#)

[Current limiting molded case circuit breaker module for series G, JG and CL](#)

[Current limiting molded case circuit breaker module product aid](#)

[Breaker service centers](#)

[J-Frame 310+ and L-Frame 310+ Molded-case circuit breakers](#)

Catalogs

[Eaton's Volume 4—Circuit Protection](#)

[Molded case circuit breakers catalog](#)

Drawings

[LG-frame Molded Case Circuit Breaker Drawing](#)

Installation instructions

[Installation Instructions for Series G L-Frame Circuit Breakers](#)

Specifications and datasheets

[NG and ND-Frame molded case circuit breakers](#)

[Eaton Specification Sheet - LGE3350FAG](#)

[L-Frame 310+ Molded-case circuit breakers 100A-600A](#)

[MOEM MCCB product selection guide](#)

Time/current curves

[Series G, L-frame Time Current Curves](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)