



FEATURES

- Compact, open body linear high bay offers energy efficient performance
- Easy center-ballast cover allows tool-less access without lamp or reflector removal
- Extremely low profile—only 2" overall height allows fixture to be installed without concern about obstructions
- Reflector options include uplight (recommended) or solid top with either narrow or wide distribution
- Rotary locking lampholders secure lamp in position and conceal contacts
- Easy field-installed accessories or factory-installed options for sensors, wire guards, lenses
- Quick and simple hanging systems including chain, tong, pipe hanger, or aircraft mounting
- Suitable for operation in up to a 45°C (113°F) ambient environment

ORDERING INFORMATION

LHA	4										
SIZE	4 4'	LAMP TYPE	32 4', T8: 32 Watt 54 4', T5HO: 54 Watt	UPLIGHT	ST Solid Top U Uplight	BALLAST FACTOR	BLANK 0.88BF for T8, 1.00BF for T5HO HL 1.18BF High Lumen T8, N/A for T5HO Lamp Type	VOLTAGE	U 120V-277V 347 347V 480 480V	OPTIONS	C6TL15_ 6' Cord and Twist-Lock™ Plug 15A (Add Voltage: 1=120, 2=277) C6TL20_ 6' Cord and Twist-Lock™ Plug 20A (Add Voltage 1=120, 2=277) C6P151 6' Cord and Straight Blade Plug 15A, 120V CA Clear Acrylic Lens ² CP Clear Polycarbonate Lens ² CAWG Clear Acrylic Lens and Flat Wire Guard ² CPWG Clear Polycarbonate Lens and Flat Wire Guard ² SP Side Panels Installed ² WG Flat Wire Guard ² TC Steel Top/Side Covers Installed ² EL141 1400 Lumens, Emergency Battery Pack T8 1-Lamp EL5H 1250 Lumens, Emergency Battery Pack T5HO 1-Lamp F3C5 3-Conductor Cord F4C5 4-Conductor Cord OS1360 Factory Installed Occupancy/Daylight Sensor, with 360° lens, 120/277/347V OS2360 Factory Installed Occupancy/Daylight Sensor, with 360° lens, 120/277/347V OS1A Factory Installed Occupancy/Daylight Sensor, with Aisle lens, 120/277/347V OS2A Factory Installed Occupancy/Daylight Sensor, with Aisle lens, 120/277/347V OS480360 Factory Installed Occupancy/Daylight Sensor, with 360° lens, 120/277/347V OS480A Factory Installed Occupancy/Daylight Sensor, with Aisle lens, 120/277/347V
MODEL	LHA Industrial Fluorescent High Bay	REFLECTOR	N Narrow Distribution W Wide Distribution	BALLAST	LHA4-454 EP (2) 2-Lamp Electronic T5HO, Programmed Start 4EP (1) 4-Lamp Electronic T5HO, Programmed Start LHA4-432 E (2) 2-Lamp Electronic T8, Instant Start EP (2) 2-Lamp Electronic T8, Programmed Start 4E (1) 4-Lamp Electronic T8, Instant Start 4EP (1) 4-Lamp Electronic T8, Programmed Start LHA4-654 24EP (1) 2-Lamp & (1) 4-Lamp Electronic T5HO, Programmed Start LHA4-632 3E (2) 3-Lamp Electronic T8, Instant Start 3EP (2) 3-Lamp Electronic T8, Programmed Start 24E (1) 2-Lamp & (1) 4-Lamp Electronic T8, Instant Start 24EP (1) 2-Lamp & (1) 4-Lamp Electronic T8, Programmed Start	LAMPS INSTALLED	T8 F0835 32 Watt, 82 CRI, 3500K F0841 32 Watt, 82 CRI, 4100K F0850 32 Watt, 82 CRI, 5000K T5HO F554835 54 Watt, 85 CRI, 3500K F554841 54 Watt, 85 CRI, 4100K F554850 54 Watt, 85 CRI, 5000K				
NO. OF LAMPS	4 Four 6 Six										
ACCESSORIES (ORDER SEPARATELY)											
LHVTH ³	Tong Hanger (Pair)										
LHVWG4-4	Wireguard, White, 4-Lamp Fixture										
LHVWG4-6	Wireguard, White, 6-Lamp Fixture										
LHVQM5	Aircraft Cable, 5' (Pair)										
LHVQM10	Aircraft Cable, 10' (Pair)										
LHVSPM5	Single Point Mounting, Includes Pair of 5' Aircraft Cables										
LHVSP	Side Panels (Pair)										
LHVOS1360	Occupancy/Daylight Sensor, with a 360° lens, 120/277/347V										
LHVOS2360	Occupancy/Daylight Sensor, with a 360° lens, 120/277/347V										
LHVOS480360	Occupancy/Daylight Sensor, with a 360° lens, 480V										
C6TL15-120	Cord and Plug Kit (white), 6 ft., Twist Lock NEMA L5-15P, 15 amp, 120V										
C6TL15-277	Cord and Plug Kit (white), 6 ft., Twist Lock NEMA L7-15P, 15 amp, 277V										
C6P15-120	Cord and Plug Kit (white), 6 ft., Straight Blade NEMA 5-15P, 15 amp, 120V										

¹Use programmed start ballast. Not recommended for use with instant start. For more occupancy/daylight harvesting sensor accessories see page 98.

²Side panels/top covers or shielding options increase height to 27/8".

³Not available with EL141 or EL5H.

PRODUCT AVAILABILITY

MODEL	SOURCE	NO. OF LAMPS	UPLIGHT OPTIONS	LAMP TYPE	WIDTH	LENGTH	HEIGHT ²
LHA	T5HO, T8	4	U, ST	32, 54	16 ³ / ₁₆ "	48"	2"
	T5HO, T8	6	U, ST	32, 54	20 ⁵ / ₁₆ "	48"	2"