



OUTDOOR BOWL KITS

CFL



EPACT Model **OLK200CFL-(Finish)**
 Bulb Type **Medium Base CFL**
 Max. Watt **1-13W CFL (Included)**
 Glass Finish **Clear Water**
 Finish Options **ABZ, BR, FB, RI, W**
 Height **10.47"**
 Width **6.3"**

CFL



EPACT Model **LK984-(Finish)**
 Bulb Type **Medium Base CFL**
 Max. Watt **1-18W CFL (Included)**
 Glass Finish **No Glass**
 Finish Options **GV, AGV, BR, FB, RI, ABZ**
 Height **6.5"**
 Width **12.0"**

CFL



EPACT Model **OLK124CFL-(Finish)**
 Bulb Type **Medium Base CFL**
 Max. Watt **2-13W CFL (Included)**
 Glass Finish **Amber Glass (AG, RI) White Glass Only (BN, OB, W)**
 Finish Options **AG, BN, OB, RI, W**
 Height **6.0"**
 Width **10.0"**

CFL



EPACT Model **OLK215CFL**
 Bulb Type **Medium Base CFL**
 Max. Watt **2-13W CFL (Included)**
 Glass Finish **Alabaster**
 Height **7.75"**
 Width **10.75"**

CFL



EPACT Model **OLK715CFL**
 Bulb Type **Medium Base CFL**
 Max. Watt **2-13W CFL (Included)**
 Glass Finish **Tea-Stained**
 Height **7.75"**
 Width **10.75"**

CONVERTIBLE PENDANTS/LIGHT KITS

CFL



EPACT Model **MNRLK-(Finish)**
 Bulb Type **Medium Base CFL**
 Max. Watt **2-13W CFL (Included)**
 Glass Finish **Opal White**
 Finish Options **TS, OBG**
 Height **7.75"**
 Width **10.75"**

36" Drop rod (2-16" and 2-12" rods Included)



As Light Kit

CFL



EPACT Model **SELK-SPZ**
 Bulb Type **Medium Base CFL**
 Max. Watt **2-13W CFL (Included)**
 Glass Finish **Creamy Frosted**
 Finish Options **Spanish Bronze**
 Height **14"**
 Width **13.75"**



As Light Kit



OUTDOOR BOWL KITS

CFL



EPACT Model **OLK200CFL-(Finish)**
 Bulb Type **Medium Base CFL**
 Max. Watt **1-13W CFL (Included)**
 Glass Finish **Clear Water**
 Finish Options **ABZ, BR, FB, RI, W**
 Height **10.47"**
 Width **6.3"**

CFL



EPACT Model **LK984-(Finish)**
 Bulb Type **Medium Base CFL**
 Max. Watt **1-18W CFL (Included)**
 Glass Finish **No Glass**
 Finish Options **GV, AGV, BR, FB, RI, ABZ**
 Height **6.5"**
 Width **12.0"**

CFL



EPACT Model **OLK124CFL-(Finish)**
 Bulb Type **Medium Base CFL**
 Max. Watt **2-13W CFL (Included)**
 Glass Finish **Amber Glass (AG, RI) White Glass Only (BN, OB, W)**
 Finish Options **AG, BN, OB, RI, W**
 Height **6.0"**
 Width **10.0"**

CFL



EPACT Model **OLK215CFL**
 Bulb Type **Medium Base CFL**
 Max. Watt **2-13W CFL (Included)**
 Glass Finish **Alabaster**
 Height **7.75"**
 Width **10.75"**

CFL



EPACT Model **OLK715CFL**
 Bulb Type **Medium Base CFL**
 Max. Watt **2-13W CFL (Included)**
 Glass Finish **Tea-Stained**
 Height **7.75"**
 Width **10.75"**

CONVERTIBLE PENDANTS/LIGHT KITS

CFL



EPACT Model **MNRLK-(Finish)**
 Bulb Type **Medium Base CFL**
 Max. Watt **2-13W CFL (Included)**
 Glass Finish **Opal White**
 Finish Options **TS, OBG**
 Height **7.75"**
 Width **10.75"**

36" Drop rod (2-16" and 2-12" rods Included)



As Light Kit

CFL



EPACT Model **SELK-SPZ**
 Bulb Type **Medium Base CFL**
 Max. Watt **2-13W CFL (Included)**
 Glass Finish **Creamy Frosted**
 Finish Options **Spanish Bronze**
 Height **14"**
 Width **13.75"**



As Light Kit