



LAMP HOLDERS

LED Swivel Floodlights
1000 Lumen 13W LED

D23.2



Catalog #: LL1000W

APPLICATIONS

For general outdoor lighting in wet, damp or dry locations
May be used with BELL® cluster covers and boxes

PRODUCT FEATURES

- Rugged die cast construction
- State-of-the-art powder coat finish provides maximum weatherability and scratch resistance
- Patented multi-directional swivel joint
- Tempered Glass Lens
- Long Life: 50,000 hours
- Patented no-tool easy-mount feature
- Warranty: 5 year
- Color: White
- 120V 60 Hz
- N/A

CULUS

File E464682

NEMA

3R Rated

NEC

2014 Compliant

US PATENTS

7,695,170

GENERAL PRODUCT INFORMATION

Color: White

PRODUCT MEASUREMENTS

Wt. Ea. (Lbs.): 0.895

PACKAGING

Package Type:	Clear Box
Std. Pkg.:	4
Product UPC-A Labeled:	Yes
Weight (Lbs. Per/C):	89.5
Ship Carton Length (in.):	17.38
Ship Carton Width (in.):	4.25
Ship Carton Height (in.):	4.75
Ctn Weight (Lbs.):	3.4
Pallet Qty:	1536
UPC Number:	050169917565
I2of5:	50050169917560