



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LL107SA 4" Alu LL Cond Body

Appleton/Oz Gedney

Catalog Number	LL107SA
Manufacturer	Appleton/Oz Gedney
Description	Imc/Rigid Conduit Body, Access Opening Left Side, Configuration LL, Cover Type Epoxy Powder Coated Cast Copper Free Aluminum, Hub Location 90 Deg, Number Of Hubs 2, Hub Size 4 Inch, Size 12.69 Inch L X 6.94 Inch W, Installation Threaded, Material Epoxy Powder Coated Copper Free Cast Aluminum Body, Neoprene Gasket, Stainless Steel Screw, Form Type Form 7, Approval UI 514A/514B/E2527, Csa C22.2, Used On Imc/Rigid Conduit, Applicable Standard Nec/Cec, Nema FB-1, Capacity 244 Cu Inch
Weight per unit	15.0 (lbs/each)
Product Category	Alum

Descriptions

Description	4" ALU LL COND BODY
extra long description	APP LL107-SA 4 FM7 ALUMINUM BODY
Long Description	IMC/Rigid Conduit Body, Access Opening Left Side, Configuration LL, Cover Type Epoxy Powder Coated Cast Copper Free Aluminum, Hub Location 90 Deg, Number of Hubs 2, Hub Size 4 Inch, Size 12.69 Inch L x 6.94 Inch W, Installation Threaded, Material Epoxy Powder Coated Copper Free Cast Aluminum Body, Neoprene Gasket, Stainless Steel Screw, Form Type Form 7, Approval UL 514A/514B/E2527, CSA C22.2, Used On IMC/Rigid Conduit, Applicable Standard NEC/CEC, NEMA FB-1, Capacity 244 Cu Inch
Product Type	4 FM7 Aluminum Body

Manufacturer Information

Brand	Appleton
GTIN	00781381606677
Manufacturers Part Number	LL107-SA
UPC	781381606677

Taxonomies, Classifications, and Categories

Category Description	FORM 7, 8, CONDULETS, COVERS, & GASKETS
----------------------	---

Packaging

Carton	1
Weight Per each	15