



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LMM01 3/8" DC Sealight STR Conn

Appleton/Oz Gedney

Catalog Number	LMM01
Manufacturer	Appleton/Oz Gedney
Description	Zinc LMM Straight Liquidtight Connector, 3/8 In Trade Size, Insulated, 1.49 In Body Length, 0.53 In Thread Length, 1.28 In Dia
Weight per unit	0.1300 (lbs/each)
Product Category	Liquid Tight Fittings

Features

angle	Straight
connection	Male NPS Thread
Connector Type	Compression
insulation	Non Insulated
Material	Zinc Die Cast

Material, Color, and Finish

Color	Metallic
Finish	Natural

Dimensions and Weight

Size	0.375
------	-------

Descriptions

Description	3/8" DC SEALTIGHT STR CONN
extra long description	EGS LMM-01 3/8 IN CONN LFMC/LFNC
Long Description	Zinc LMM Straight Liquidtight Connector, 3/8 IN Trade Size, Insulated, 1.49 IN Body Length, 0.53 IN Thread Length, 1.28 IN Dia
Product Type	3/8 In Conn LFMC/LFNC
Special Features	1.28 IN Dia X 1.49 IN Length, 0.53 IN Thread Length, For Liquidtight Flexible Metal Conduit and Type B Non-Metallic Conduit, Liquidtight/Raintight/Oiltight

Manufacturer Information

Brand	Appleton
GTIN	00687855382019
Manufacturers Part Number	LMM01
UPC	687855382019

Taxonomies, Classifications, and Categories

Category Description	METALLIC FITTINGS
Type	Straight Liquid Tight Conduit Connector

Trade Size

Trade Size	0.5
------------	-----



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	25
Package	100
Weight Per each	0.13

Uses, Certifications, and Standards

Application	For Terminating Liquidtight Flexible Metal Conduit to a Enclosure
environmental conditions	Rain Tight, Oil Tight, Liquid Tight
nema rating	FB-1
standard	CSA Certified L39354;CSA Certified: 208044;CSA Standard: C22.2 No. 18.3;NEMA: FB-1;UL Listed: E32539;UL Standard: 514B