



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LPCC30 30A 600V TD Class CC Low Peak Fuse

Bussmann Fuses

Catalog Number	LPCC30
Manufacturer	Bussmann Fuses
Description	Low Peak Fuse, Time Delay Fuse Speed, Class CC Fuse, 12 S @ 200% Response Time, 30 A, 600 V Ac;300 V DC, Melamine Tube Material, Dual Element, 0.41 In Diameter, 1.5 IN38.1 MM Overall Length, 0.02 LB
Weight per unit	0.0200 (lbs/each)
Product Category	Current Limiting

Features

amperage rating	30
class	Class CC
connection	Ferrule End X Ferrule End
dimensions	0.4100 IN X 0.4100 IN X 1.5000 IN
element	Dual
media	Yes

Dimensions and Weight

Size	13/32 In Diameter X 1-1/2 In Length
------	-------------------------------------

Descriptions

Description	30A 600V TD CLASS CC LOW PEAK FUSE
extra long description	BUSS LP-CC-30 LOW PEAK CC TIME DELA
Features	Bussmann's Class CC fuses set the standard in Class CC fuse performance in the industry. Recognized for their superior performance, Bussmann has the right product for your circuit and equipment protection needs. These branch circuit rated, 600v, 200,000a IR fuses offer exceptional protection in the smallest package of any UL class of fuses. Choose from the ultimate protection provided by our Low Peak LP-CC fuses, the time delay of our FNQ-R's for your control transformer and similar control applications or
Special Features	Rejection Style

Manufacturer Information

Brand	COOPER BUSSMANN
GTIN	00051712180313
UPC	051712180313

Taxonomies, Classifications, and Categories

Category Description	MIDGET FUSES
Type	FUSE



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton 10

Weight Per each 0.02

Uses, Certifications, and Standards

standard UL Listed ,CSA Certified,RoHS Compliant,CE Marked