



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LSS11SRL Mini Din Switch Assy LS-S11S Switch Body+LS-XRL He

Eaton Corp

Catalog Number	LSS11SRL
Manufacturer	Eaton Corp
Description	Eaton LS-Titan Miniature Din Limit Switch, Side Rotary, Polyamide PA66-GF25 Enclosure, 6A Max Ac, 3A Max DC, 1NO-1NC, Snap Action, Positive Opening, 6A At 240VAC, 3A At 24VDC, Screw Terminals
Weight per unit	0.1500 (lbs/each)
Product Category	Limit Switch Accessories

Features

connection	Screw Terminal
Contact Configuration	1 NO-1 NC, snap action, positive opening
Contact Rating	6A at 240Vac, 3A at 24Vdc
dimensions	1.2200 IN X 1.8200 IN X 4.3400 IN

Descriptions

Description	MINI DIN SWITCH ASSY LS-S11S SWITCH BODY+LS-XRL HE
extra long description	ETN LS-S11S-RL IEC LIMIT SWITCH ASS
Features	Eaton's LS-Titan limit switch line is a complete offering of safety position switches designed for worldwide application. Economical insulated plastic or rugged metal enclosures and modular, plug-in operating heads and bodies make the LS-Titan a flexible switching solution.
Long Description	Eaton LS-Titan Miniature DIN Limit Switch, Side Rotary, Polyamide PA66-GF25 enclosure, 6A max AC, 3A max DC, 1NO-1NC, Snap Action, Positive Opening, 6A at 240Vac, 3A at 24Vdc, Screw Terminals
Product Type	IEC Limit Switch Assy, LS-S11S+LS-XRL

Manufacturer Information

Brand	Eaton
GTIN	00786685392769
Manufacturers Part Number	LS-S11S-RL
UPC	786685392769

Taxonomies, Classifications, and Categories

Type	Miniature DIN IEC limit switch
------	--------------------------------

Packaging

Carton	1
Weight Per each	0.15



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Elec Assemblies, Panels & OEM - Electrical Assemblies and
OEMs - Other

standard

UL Listed, RoHS Compliant