

# Eaton LS-S11S-RL

Catalog Number: LS-S11S-RL

Eaton LS-Titan Miniature DIN Limit Switch, Side Rotary, Polyamide PA66-GF25 enclosure, 6A max AC, 3A max DC, 1NO-1NC, Snap Action, Positive Opening, 6A at 240Vac, 3A at 24Vdc, Screw Terminals



Photo is representative

## General specifications

Product Name	Catalog Number
Eaton LS-Titan miniature DIN limit switch	LS-S11S-RL
UPC	Product Length/Depth
786685392769	1.22 in
Product Height	Product Width
4.34 in	1.82 in
Product Weight	Warranty
0.1438 lb	1 year
Compliances	Certifications
RoHS Compliant	UL Listed

## defaultTaxonomyAttributeLabel

### Type

LS-Titan

### Contact Rating

6A at 240Vac, 3A at 24Vdc

### Enclosure material

Polyamide PA66-GF25

### Connection

Screw terminal

### Contact configuration

1 NO-1 NC, snap action, positive opening

### Switch type

Side rotary

### Operating temperature - max

158 °F

### Operating temperature - min

-13 °F

### Environmental rating

IP66, IP67

### Maximum AC current

6 A

### Maximum DC current

3 A

## Resources

### Brochures

[LS-Titan Safety Limit Switches](#)

### Catalogs

[Eaton's Volume 8—Sensing Solutions](#)

### Specifications and datasheets

[Eaton Specification Sheet - LS-S11S-RL](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)