

Titan[®]

Type EF Extra-Flexible Liquidtight Metal Conduit



Extra-Flexible Liquidtight Metal Conduit. General Purpose Use. Oil-Resistant. Sunlight-Resistant. Temperature Rated - 10°C to 60°C.

APPLICATIONS

Titan[®] Extra-Flexible Liquidtight Flexible Metallic Conduit is suitable of the following installations:

- Delivers wiring protection where listed products are not required
- Seals out abrasives, alcohol, coolants, corrosive fumes and gases, dirt, grease, mineral acids, non-concentrated fixed alkaline, petroleum oils, salt air spray, water and weather
- Used in industrial and commercial applications for conveyors, blowers, cranes, air conditioners, machine tooling and lubrication equipment where UL listing is not required
- For exposed or concealed installations requiring movement, crossover connections, or tight bends

CONSTRUCTION

Titan[®] Type EF is manufactured with a spiral wound interlocked strip of corrosion-resistant, galvanized steel. A flame retardant, flexible PVC jacket is extruded over the metal core. The gray jacket resists oils, mild acids and exposure to sunlight. Black jacket available but subject to economic order quantity. REACH/RoHS-2 (Chemical Limit) Compliant

FEATURES

- Resistant to weather, heat, oil, and chemical breakdown
- Smooth metal interior for easy wire pulling
- Requires standard liquid-tight fittings
- Rated for temperature range of -10°C to 60°C (14°F to 140°F)



®Ultratite is a registered trademark of Southwire Company, LLC

Titan - Type EF

The Power of Connections.™



Southwire[®]

©2016 Southwire Company, LLC. All rights reserved. ®Registered Trademark of Southwire Company, LLC.
One Southwire Drive, Carrollton, GA 30119, USA

TRADE SIZE (INCHES)	STOCK NUMBER			DIAMETER (INCHES)		WEIGHT (LBS/100')	APPROX. BEND DIAMETER (INCHES)
				INNER (MIN/MAX)	OUTER (MIN/MAX)		
STEEL EF GRAY JACKET							
3/8	55-09-37-03 (100')	55-09-37-01 (500')	55-09-37-04 (600')	.484/.504	.69/.71	16	4
1/2	55-09-38-01 (100')	55-09-38-05 (500')	55-09-38-02 (1000')	.622/.642	.82/.84	16	6.5
3/4	55-09-40-03 (100')	55-09-40-05 (500')	55-09-40-02 (1000')	.82/.84	1.03/1.05	27	8.5
1	55-10-68-02 (100')	55-10-68-03 (400')		1.041/1.066	1.29/1.315	43	13
1-1/4	55-10-70-02 (50')	55-10-70-04 (250')		1.38/1.41	1.63/1.66	56	16
1-1/2	55-10-71-02 (50')	55-10-71-03 (150')		1.575/1.6	1.865/1.99	83	18
2	55-10-72-02 (50')	55-10-72-03 (100')		2.02/2.045	2.34/2.375	110	22.25
2-1/2	55-10-73-01 (25')	55-10-73-03 (150')		2.48/2.505	2.84/2.875	137	29.25
3	55-10-74-01 (25')	55-10-74-03 (100')		3.07/3.1	3.46/3.5	163	35
3-1/2	55-10-75-01 (25')	55-10-75-03 (100')		3.5/3.54	3.96/4	202	40
4	55-10-76-01 (25')	55-10-76-03 (100')		4/4.04	4.46/4.5	235	48
STEEL EF BLACK JACKET							
1/2	55-28-99-03 (100')	55-28-99-02 (1000')		.622/.642	.82/.84	20	6.5
3/4	55-29-00-03 (100')	55-29-00-02 (1000')		.82/.84	1.03/1.05	27	8.5
1-1/2	55-29-03-02 (50')			1.575/1.6	1.865/1.99	83	18
* Minimum bend radius based NEC Table 2, Chapter 9 (other bends) per Article 350.							