



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

LT3 3" Met L/T, Non UI 25' *Southwire Company*



Catalog Number	LT3
Manufacturer	Southwire Company
Description	Liquidtight Flexible Conduit, 3 In Trade Size, 3.46 to 3.5 In Conduit Outer Diameter, 3.07 to 3.1 In Conduit Inner Diameter, Titan(R) Ef Style, 25 FT Length, Galvanized, Gray, 18 In Bend Radius, +14 °F Operating Temperature, +140 °F Operating Temperature, 209 LB/100 FT
Weight per unit	1.5 (lbs/ft)
Product Category	Liquid Tight Conduit

Features

outside diameter	3415
------------------	------

Dimensions and Weight

Diameter	3"
----------	----

Descriptions

Description	3" MET L/T, NON UL 25'
extra long description	SWC 55107401 Titan2 Type EF Extra-F

Manufacturer Information

GTIN	00032886043130
UPC	032886043130

Taxonomies, Classifications, and Categories

Category Description	Liquid Tight
----------------------	--------------

Packaging

Carton	25
Weight Per foot	1.45