



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## LT38 3/8" Met L/T, Non UI 100' *Southwire Company*



Catalog Number	LT38
Manufacturer	Southwire Company
Description	Liquidtight Flexible Conduit, 3/8 In Trade Size, 0.69 to 0.71 In Conduit Outer Diameter, 0.484 to 0.504 In Conduit Inner Diameter, Titan(R) Ef Style, 100 FT Length, Galvanized, Gray, 4 In Bend Radius, +14 °F Operating Temperature, +140 °F Operating Temperature, 22 LB/100 FT
Weight per unit	0.2200 (lbs/ft)
Product Category	Liquid Tight Conduit

### Features

outside diameter	700
------------------	-----

### Dimensions and Weight

Diameter	3/8"
----------	------

### Descriptions

Description	3/8" MET L/T, NON UL 100'
extra long description	SWC 55093703 Titan2 Type EF Extra-F

### Manufacturer Information

GTIN	00032886042683
UPC	032886042683

### Taxonomies, Classifications, and Categories

Category Description	Liquid Tight
----------------------	--------------

### Packaging

Carton	100
Weight Per foot	0.22