



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LT75GSA 3/4" LT STR Conn

Crouse-Hinds

Catalog Number	LT75GSA
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Liquidator Liquidtight Connector, FMC, Straight, Aluminum Ground Lug, Non-Insulated, #4-14 Awg Lug Size, Aluminum, 3/4"
Weight per unit	0.1800 (lbs/each)
Product Category	Liquid Tight Fittings

Features

dimensions	1.9100 IN X 1.5000 IN X 2.2500 IN
Material	Aluminum

Descriptions

Description	3/4" LT STR CONN
extra long description	MIDWEST LT75G SA 3/4 LT CONN WITH G
Features	Liquidtight fittings from Eaton's Crouse-Hinds Division are designed to protect conductors from mechanical damage due to vibration and movement while sealing out cutting oils, coolants, water, and dust. Typical applications include the wiring of machine tools, motors, transformers, food processing equipment, robotics, air conditioning units and illuminated signs. To meet any customer preference, Crouse-Hinds series liquidtight fittings are available in a variety sizes, configurations and materials, inclu
Long Description	Eaton Crouse-Hinds series Liquidator liquidtight connector, FMC, Straight, Aluminum ground lug, Non-insulated, #4-14 AWG lug size, Aluminum, 3/4"
Product Type	3/4 LT Conn With Ground Lug Al

Manufacturer Information

Brand	EATON CROUSE-HINDS SERIES
GTIN	00784564340757
Manufacturers Part Number	LT75G SA
UPC	784564340757

Taxonomies, Classifications, and Categories

Category Description	METALLIC FITTINGS
Type	Liquidtight connector

Packaging

Carton	1
Package	25
Weight Per each	0.18



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Commercial / Institutional Buildings / Structures - Commercial /
Institutional Buildings / Structures - Other
