

**NEW!**

# Liquid-tight, Concrete-tight MC Cable Fittings

**for PVC Jacketed MC Cable or Teck cable • Fits Widest Cable Range**



**Ideal for  
Parking Decks  
or High Rise Residential  
Construction**




LTMC507  
components


**Easy Installation!** 1 Cut PVC jacket back 1-1/4"



2 Push jacketed MC cable into fitting



3 Insert assembly into box



Made in USA

Save time and money with Arlington's liquid-tight, concrete-tight fittings designed especially for PVC jacketed MC cable – and Teck 90 cable.

Perfect for parking decks, these new, larger sizes cover the widest cable range: 1/2 to 6/3.

They're compact - and the economical solution to installing PVC jacketed MC or Teck cable.


- cULus Listed



LTMC507

CATALOG NUMBER	UPC/DCI/NAED MFG #01 8997	DESCRIPTION	UNIT/STD PKG
<b>LTMC507</b>	16800	<b>1/2" trade size</b>	25
<b>MC Cable Range:</b>		.550" to .730"	
<b>Teck 90 Range:</b>		.580" to .765"	
<b>MC Cable Overall jacket OD:</b>		.670" to .830"	
<b>Teck 90 Overall jacket OD:</b>		.670" to .855"	

CATALOG NUMBER	UPC/DCI/NAED MFG #01 8997	DESCRIPTION	UNIT/STD PKG
<b>LTMC75</b>	16801	<b>3/4" trade size</b>	25
<b>MC Cable Range:</b>		.725" to .890"	
<b>Teck 90 Range:</b>		.765" to .980"	
<b>MC Cable Overall jacket OD:</b>		.830" to .990"	
<b>Teck 90 Overall jacket OD:</b>		.855" to 1.06"	



LTMC75



## Arlington

1 Stauffer Industrial Park  
Scranton, PA 18517  
800/233.4717  
Fax 570/562.0646  
[www.aifittings.com](http://www.aifittings.com)

NEW!

# Liquid-tight, Concrete-tight MC Cable Fittings

*for PVC Jacketed MC Cable or Teck cable • Fits Widest Cable Range*



**Ideal for  
Parking Decks  
or High Rise Residential  
Construction**




LTMC507  
components


**Easy Installation!** 1 Cut PVC jacket back 1-1/4"



2 Push jacketed MC cable into fitting



3 Insert assembly into box




Made in USA

Save time and money with Arlington's liquid-tight, concrete-tight fittings designed especially for PVC jacketed MC cable – and Teck 90 cable.

Perfect for parking decks, these new, larger sizes cover the widest cable range: 1/2 to 6/3.

They're compact - and the economical solution to installing PVC jacketed MC or Teck cable.


• cULus  
Listed



LTMC507

CATALOG NUMBER	UPC/DCI/NAED MFG #01 8997	DESCRIPTION	UNIT/STD PKG
LTMC507	16800	1/2" trade size	25
MC Cable Range:		.550" to .730"	
Teck 90 Range:		.580" to .765"	
MC Cable Overall jacket OD:		.670" to .830"	
Teck 90 Overall jacket OD:		.670" to .855"	

CATALOG NUMBER	UPC/DCI/NAED MFG #01 8997	DESCRIPTION	UNIT/STD PKG
LTMC75	16801	3/4" trade size	25
MC Cable Range:		.725" to .890"	
Teck 90 Range:		.765" to .980"	
MC Cable Overall jacket OD:		.830" to .990"	
Teck 90 Overall jacket OD:		.855" to 1.06"	



LTMC75



**Arlington**

1 Stauffer Industrial Park  
Scranton, PA 18517  
800/233.4717  
Fax 570/562.0646  
www.aifittings.com