



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## LU100MED 100W B17 High Pressure Sodium Clear Medium Base

*Ge By Current Lamps*

Catalog Number	LU100MED
Manufacturer	Ge By Current Lamps
Description	High Pressure Sodium Lamp, 22, 2100 K, 9500 LM Brightness (Lumens), 100 W, 110 V, Clear, Glass Material, 24000+ H Average Life, Mogul Base, S54ZL Ansi Ballast Code, Non Dimmable, 2.125 In Diameter, 5.43 In Length, 15.84 % Mercury Content, 0.18 LB
Weight per unit	0.1800 (lbs/each)
Product Category	Hid High Pressure Sodium Lamps

### Features

Base	Medium Screw (E26)
lumens	9500.0
Wattage	100.0

### Material, Color, and Finish

Color	Clear
color rendering index (cri)	22.0
Style	Open or enclosed fixtures

### Descriptions

Description	100W B17 HIGH PRESSURE SODIUM CLEAR MEDIUM BASE
extra long description	GEL LU100/MED/ECO 13250 LUCALOX
Special Features	5.5IN Length

### Manufacturer Information

Brand	Ge Traditional Lamps
GTIN	00043168132503
UPC	043168132503

### Taxonomies, Classifications, and Categories

Category Description	SODIUM
----------------------	--------

### Packaging

Carton	1
Package	6
Weight Per each	0.18