



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LU400HECO 400W HPS ED18 Clear Bulb Mog Screw Base 2100K Lamp

Ge By Current Lamps

Catalog Number	LU400HECO
Manufacturer	Ge By Current Lamps
Description	High Pressure Sodium Lamp, 22, 614 K, 51000 LM Brightness (Lumens), 400 W, 198 V, Clear, Glass Material, 24000+ H Average Life, E39 Mogul Screw Base, S51 Ansi Ballast Code, Non Dimmable, 2.25 In Diameter, 9.75 In Length, 15.84 % Mercury Content, 0.42 LB
Weight per unit	0.4200 (lbs/each)
Product Category	Hid High Pressure Sodium Lamps

Features

Base	Mogul Screw (E39)
lumens	51000.0
Wattage	400.0

Material, Color, and Finish

Color	Clear
color rendering index (cri)	22.0
Finish	Clear
Style	Open or enclosed fixtures

Descriptions

Description	400W HPS ED18 CLEAR BULB MOG SCREW BASE 2100K LAMP
extra long description	GEL LU400/H/ECO 85379 LUCALOX
Special Features	9.75IN Length

Manufacturer Information

Brand	Ge Traditional Lamps
GTIN	00043168853798
Manufacturers Part Number	LU400/H/ECO
UPC	043168853798

Taxonomies, Classifications, and Categories

Category Description	SODIUM
----------------------	--------

Packaging

Carton	1
Package	12
Weight Per each	0.42

Uses, Certifications, and Standards

Application	Universal burning position
-------------	----------------------------