



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

IMAGE
COMING
SOON

M175SUPER5KIT Ballast Lamp

Sylvania-Ledvance

Catalog Number	M175SUPER5KIT
Manufacturer	Sylvania-Ledvance
Description	OBS47243 120/208/240/277/480V 5 Tap Magnetic Core and Coil Probe Start Ballast For 175W Probe Start Metal Halide Lamp
Weight per unit	8.4 (lbs/each)
Product Category	Lighting

Features

amperage rating	1.96, 1.15, 1, 0.86, 0.54
ANSI Code	M57
Ballast Factor	1
Lamp Type	METALARC METAL HALIDE MAGNETIC
Minimum Starting Temperature	-22.000000000000000
Number of Lamps	1
Power Factor	>0.9
start type	Pulse
total harmonic distortion	<20
Voltage Rating	120, 208, 240, 277, 480
Wattage	175

Dimensions and Weight

Height	3.000000000000000
Length	4.000000000000000
Width	4.000000000000000

Descriptions

Description	BALLAST LAMP
extra long description	SYL M175/SUPER5-KIT/47243 M175SUPER
Long Description	OBS47243 120/208/240/277/480V 5 tap magnetic core and coil probe start ballast for 175W probe start metal halide lamp
Product Type	M175SUPER5KIT 1/CS 1/Sku
Special Features	Multi Tap, Magnetic Core and Coil, Circuit Type Constant Wattage Autotransformer, Input Power 210 WAT, Open Circuit Voltage 305 V, Ground Ballast Core

Manufacturer Information

Brand	OSRAM
GTIN	00046135472435
Manufacturers Part Number	M175/SUPER5-KIT/47243
UPC	046135472435



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description UNIVERSAL BALLAST UNV

Type Magnetic HID Ballast

Packaging

Carton 1

Weight Per each 8.36

Uses, Certifications, and Standards

standard cUL, M57