

# Eaton M22-LEDC230-G

Catalog Number: M22-LEDC230-G

Eaton M22 modular pushbutton, LED Light Unit, Base, Screw, IP66, NEMA 4X, 13, Rk resistance 1, Illuminated, Green, 85-264V

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton M22 modular pushbutton	M22-LEDC230-G
<b>UPC</b>	<b>Product Length/Depth</b>
786685277745	1.46 in
<b>Product Height</b>	<b>Product Width</b>
1.03 in	1.18 in
<b>Product Weight</b>	<b>Warranty</b>
.026 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>Compliances</b>	<b>Certifications</b>
GoST-R Bureau Veritas CE Marked	CCC Marked CSA Certified Lloyd's Register Certified



## Product specifications

### Light color

Green

### Series

M22

### Type

Light Unit

### Environmental rating

IP66, NEMA 4X, 13, Rk resistance 1

### Illumination

Illuminated

### Size

22.5 mm

### Voltage rating

85-264 V

### Actuator

Base, screw

## Resources

### Brochures

[M22 Pilot Devices](#)

### Catalogs

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)

### Installation instructions

[M22 Operators and Accessories](#)

### Specifications and datasheets

[Quick Selector - M22 Pushbuttons](#)

[Eaton Specification Sheet - M22-LEDC230-G](#)

[Global Data Sheet - M22-LEDC230-G](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)