

# Eaton M22-L-Y

Catalog Number: M22-L-Y

Eaton M22 modular pushbutton, Indicating Light Operator, Flush, IP66, NEMA 4X, 13, Rk resistance 470, 22.5 mm, Yellow, Illuminated, White, 100, 000 Hours of operation



## General specifications

### Product Name

Eaton M22 modular pushbutton

### Catalog Number

M22-L-Y

### UPC

786685278650

### Product Length/Depth

2 in

### Product Height

1 in

### Product Width

2 in

### Product Weight

0.1 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Compliances

Bureau Veritas  
CE Marked  
GoST-R

### Certifications

CCC Marked  
CSA Certified  
Lloyd's Register Certified

### Catalog Notes

Includes contact block mounting adapter.

## Type

Indicating Light

## Environmental rating

IP66, NEMA 4X, 13, Rk resistance 470

## Operating Cycles

100,000 Hours of operation

## Illumination

Illuminated

## Series

M22

## Size

22.5 mm

## Actuator

Flush

## Button color

Yellow

## Light color

White

## Brochures

[M22 Pilot Devices](#)

## Catalogs

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)

## Drawings

[M22-L 3D Inventor](#)[M22-L AutoCAD 2D Footprint \(mm\)](#)[M22-L AutoCAD 2D Footprint](#)[M22-L 2D PDF](#)[M22-L 2D Drawing Xchange](#)[M22-L 3D Model Xchange](#)

## Installation instructions

[M22 Operators and Accessories](#)

## Specifications and datasheets

[Global Data Sheet - M22-L-Y](#)[Eaton Specification Sheet - M22-L-Y](#)

Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)