

Eaton M22-XD-SWRGYB

Catalog Number: M22-XD-SWRGYB

Eaton M22 pushbutton button plate, M22 Button Plate, 22.5 mm, Flush, Non-illuminated, Button: Black, white, red, green, yellow, blue, IP67, IP69K, NEMA 4X, 21

General specifications



Product Name

Eaton M22 pushbutton button plate

UPC

786685273624

Product Height

0.01 in

Product Weight

0.009 lb

Compliances

GoST-R

Bureau Veritas

CE Marked

Catalog Number

M22-XD-SWRGYB

Product Length/Depth

1 in

Product Width

1 in

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

CCC Marked

CSA Certified

Lloyd's Register Certified



Powering Business Worldwide

defaultTaxonomyAttributeLabel

Type

Button plate

Button color

Black, white, red, green, yellow, blue

Actuator

Flush

Illumination

Non-illuminated

Series

M22

Environmental rating

IP67, IP69K, NEMA 4X, NEMA 21

Size

22.5 mm

Resources

Brochures

[M22 Pilot Devices](#)

Catalogs

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)

Installation instructions

[M22 Operators and Accessories](#)

Specifications and datasheets

[Eaton Specification Sheet - M22-XD-SWRGYB](#)

[Global Data Sheet - M22-XD-SWRGYB](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)