



HAMMER-ON FLANGE CLIP, BOTTOM MOUNT WITH STUD, SPRING STEEL, 5/16"–1/2" FLANGE

CATALOG NUMBER

M58S



CERTIFICATIONS



FEATURES

Can be used to support boxes, fixtures or other applications from beam flanges

Captive threaded stud minimizes the need for additional hardware

Assorted attachment points provided to reduce inventory

Requires only a hammer to install

PRODUCT ATTRIBUTES

Material: Spring Steel

Finish: nVent CADDY Armour

Flange Thickness (FT): 5/16" - 1/2"

Rod Size (RS): 1/4"

Screw Diameter (Sc): 1/4"


Screw Length (L): 3/8"

Static Load 1 (F1): 100lb

Static Load 2 (F2): 75lb

Static Load 3 (F3): 25lb

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:
nVent.com **CADDY ERICO HOFFMAN RAYCHEM SCHROFF**
TRACER



HAMMER-ON FLANGE CLIP, BOTTOM MOUNT WITH STUD, SPRING STEEL, 5/16"-1/2" FLANGE

CATALOG NUMBER

M58S



CERTIFICATIONS



FEATURES

Can be used to support boxes, fixtures or other applications from beam flanges

Captive threaded stud minimizes the need for additional hardware

Assorted attachment points provided to reduce inventory

Requires only a hammer to install

PRODUCT ATTRIBUTES

Material: Spring Steel

Finish: nVent CADDY Armour

Flange Thickness (FT): 5/16" - 1/2"

Rod Size (RS): 1/4"

Screw Diameter (Sc): 1/4"


Screw Length (L): 3/8"

Static Load 1 (F1): 100lb

Static Load 2 (F2): 75lb

Static Load 3 (F3): 25lb

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:
nVent.com **CADDY ERICO HOFFMAN RAYCHEM SCHROFF**
TRACER