

Eaton MB2040B200BTS

Catalog Number: MB2040B200BTS

Eaton resi meter breaker, All-in-ones, 200A, C, Aluminum, NEMA 3R, Bottom and top, #6-350 kcm10 kAIC, #6-350 kcmBW2200, Surface mounting, 40, Four-jaw, 1, 20, Single-phase, Ringless, Used with BR breakers, 120/240 Vac



General specifications

Product Name	Catalog Number
Eaton residential meter breaker	MB2040B200BTS
UPC	Product Length/Depth
782114858639	5.38 in
Product Height	Product Width
32.38 in	14.44 in
Product Weight	Warranty
42 lb	10 year
Certifications	
UL Listed	

defaultTaxonomyAttributeLabel

Type

All-in-ones

Utility approvals

AL : Alabama Power

ME : Central Maine Power

AR : Entergy

LA : Entergy

MS : Entergy

TX : Entergy

CA : Pacific Gas and Electric (PG&E)

FL : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

IN : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

KY : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

NC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

OH : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

SC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

NC : Dominion

VA : Dominion

Interrupt rating

10 kAIC

Box size

C

Enclosure

NEMA 3R

Ground

#6-350 kcmil

Amperage Rating

200 A

Line

#6-350 kcmil

Mounting

Surface mounting

Number of spaces

Resources

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Drawings

Dimensional Drawing - METER BREAKER EAST COAST STYLE

Specifications and datasheets

Eaton Specification Sheet - MB2040B200BTS

Technical Data Residential Meter Breakers: Type CH and BR Residential

20

Security

Ringless

Voltage rating

120/240V

Number of sockets

1

Phase

Single-phase

Number of circuits

40

Bus material

Aluminum

Feed type

Top/bottom

Main circuit breaker

BW2200

Number of jaws

Four-jaw



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)