

Eaton MBB200BTS

Catalog Number: MBB200BTS

Eaton resi meter breaker, Meter mains, 200A, C, Aluminum, NEMA 3R, Bottom and top, #6-350 kcm10 kAIC, #6-350 kcmCSR2200, Surface mounting, Four-jaw, 1, Single-phase, Ringless, 120/240 Vac



General specifications

Product Name	Catalog Number
Eaton residential meter breaker	MBB200BTS
UPC	Product Length/Depth
782114860199	5.38 in
Product Height	Product Width
25 in	14.44 in
Product Weight	Warranty
33 lb	10 year
Certifications	
UL Listed	

defaultTaxonomyAttributeLabel

Type

Meter mains

Utility approvals

ME : Central Maine Power

FL : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

IN : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

KY : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

NC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

OH : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

SC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

IN : Indiana Michigan Power (IMP) (AEP East)

MI : Indiana Michigan Power (IMP) (AEP East)

OH : AEP Ohio (AEP East)

TN : Appalachian Power (AEP East)

VA : Appalachian Power (AEP East)

WV : Appalachian Power (AEP East)

NC : Dominion

VA : Dominion

Interrupt rating

10 kAIC

Box size

C

Enclosure

NEMA 3R

Ground

#6-350 kcmil

Voltage rating

120/240 V

Number of sockets

1

Phase

Single-phase

Bus material

Resources

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Drawings

[Dimensional Drawing - METER BREAKER EAST COAST STYLE](#)

Specifications and datasheets

[Technical Data Residential Meter Breakers: Type CH and BR Residential](#)

[Eaton Specification Sheet - MBB200BTS](#)

Aluminum

Feed type

Top/bottom

Main circuit breaker

CSR2200

Number of jaws

Four-jaw



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia