



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Eaton's Meter Breaker EUSERC

**MBE1224B100BTS**

**UPC:**782114890790

**Dimensions:**

- **Height:** 23.88 IN
- **Length:** 5.38 IN
- **Width:** 14.44 IN

**Weight:**34 LB

**Warranties:**

- 10 year

**Specifications:**

- **Type:** All-in-ones
- **Amperage Rating:** 100A
- **Box Size:** A
- **Bus Material:** Aluminum
- **Enclosure:** NEMA 3R
- **Feed Type:** Top/bottom
- **Ground:** #14-2/0 AWG
- **Interrupt Rating:** 10 kAIC
- **Line:** #6-250 kcmil
- **Main Circuit Breaker:** BR2100
- **Mounting:** Surface
- **Number Of Circuits:** 24
- **Number Of Jaws:** Four-jaw
- **Number Of Sockets:** 1
- **Number Of Spaces:** 12
- **Phase:** Single-phase
- **Security:** Ring
- **Used With:** Type BR breakers
- **Voltage Rating:** 120/240V

**Supporting documents:**

- [Dimensional Drawing - METER BREAKER WEST COAST STYLE](#)
- [Eatons Volume 1-Residential and Light](#)



Commercial

- [Technical Data Residential Meter Breakers:  
Type CH and BR Residential](#)

**Certifications:**

- UL Listed

**Product compliance:**

- EUSERC Approved

---

© 2016 Eaton. All rights reserved.