

Eaton MBX2040B150BTS

Catalog Number: MBX2040B150BTS

Eaton resi meter breaker, All-in-ones, 150A, Aluminum, NEMA 3R, Bottom and top, #6-350 kcm22 kAIC, #6-350 kcmCSR, Surface mounting, 40, Four-jaw, 1, 20, Single-phase, Ringless, Black Hills Energy, 120/240 Vac, Lever bypass



Photo is representative

General specifications

Product Name	Catalog Number
Eaton residential meter breaker	MBX2040B150BTS
UPC	Product Length/Depth
786685460635	4.93 in
Product Height	Product Width
39.81 in	14.19 in
Product Weight	Warranty
40 lb	10 year
Certifications	
UL Listed	

defaultTaxonomyAttributeLabel

Type

All-in-ones

Utility approvals

IL : Ameren

MO : Ameren

CO : Xcel Energy

MI : Xcel Energy

MN : Xcel Energy

ND : Xcel Energy

NM : Xcel Energy

SD : Xcel Energy

TX : Xcel Energy

WI : Xcel Energy

Interrupt rating

22 kAIC

Enclosure

NEMA 3R

Ground

#6-350 kcmil

Voltage rating

120/240 V

Number of sockets

1

Phase

Single-phase

Bypass

Lever

Number of circuits

40

Bus material

Aluminum

Feed type

Top/bottom

Main circuit breaker

CSR

Number of jaws

Four-jaw

Resources

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Drawings

[Dimensional Drawing - C-H SKT/BKR COMBO 150A](#)

Specifications and datasheets

[Eaton Specification Sheet - MBX2040B150BTS](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)