



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



MCSTAT122BLWH250 12/2 WG Steel MC Stat BL/WH 7504-42-05 *Southwire Company*

Catalog Number	MCSTAT122BLWH250
Manufacturer	Southwire Company
Description	12-2 Solid Blue, White, Green - MC Stat®, Green Interlocked Galvanized Steel Armor With Phase Id - Type Mci-A - Health Care Facilities - 250' Coil
Weight per unit	0.1590 (lbs/ft)
Product Category	Teck

Features

Bend Radius	7.845
Conductor Size	12
gauge	12 AWG
Inside Diameter	0.343
Material	Galvanized Steel
Number of Conductors	4
outside diameter	0.523
Voltage Rating	600V

Material, Color, and Finish

Color	Green
Conductor Material	Copper
Finish	Lime Green Paint

Dimensions and Weight

Length	250
--------	-----



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	12/2 WG STEEL MC STAT BL/WH 7504-42-05
extra long description	AFC 7504-42-05 12-2 STATST 250C
Features	MC Stat® is a healthcare version of traditional MC Cable, incorporating the redundant ground required for NEC 517.13. The armor in combination with full-sized aluminum ground/bonding conductor, along with the full-sized green insulated copper grounding conductor, provide the necessary grounding redundancy in healthcare settings. MC Stat®'s unique features, including its wrap-free design, ColorSpec®ID/ColorTrak® ID, and Patented Polypropylene covered THHN/THWN-rated conductors, make it a reliable and efficient
Long Description	12-2 Solid Blue, White, Green - MC Stat®, Green Interlocked Galvanized Steel Armor with phase ID - Type MCI-A - Health Care Facilities - 250' Coil
Product Type	12-2 Statst 250C
Short Description	12-2 STATST 250C

Manufacturer Information

Brand	Flexible Conduit
GTIN	00077680254788
Manufacturers Part Number	7504-42-05
UPC	077680254788

Taxonomies, Classifications, and Categories

Category Description	BX & MC
Type	MC-Stat® Steel Cable

Trade Size

Trade Size	12-2
------------	------

Packaging

Carton	250
Weight	0.1598
Weight Per foot	0.159

Uses, Certifications, and Standards

standard	UL 1569, UL 83, UL 1479, UL 1581, UL 2556, E80042 Federal spec A-A-59544 (formerly J-C-30B) NEC® 330, 300.22(C), 230.43, 250.118, 392, 396, 503, 530, 517, 518, 520, 645 UL Classified 1, 2, and 3 hour through (Fire) penetration product, R-14141 NEC® 300.22(C) Environmental Air Handling Spaces
Temperature Rating	194