



**Description** 400W ED-37 Mogul Base Universal Burn  
**Ordering Code** 49197  
**UNSPSC Code** 39101614

## Specifications

<b>Watts</b>	400
<b>Base Type</b>	Mogul Screw (E39)
<b>Bulb Type</b>	ED-37
<b>MOL in/mm</b>	11.5/292.1
<b>MOD in/mm</b>	4.65/118.0
<b>LCL in/mm</b>	7.00/178.0
<b>Approx Initial Lumens</b>	36000
<b>Approx Mean Lumens</b>	23000
<b>CT deg K</b>	4000
<b>CRI</b>	70
<b>Rated Life</b>	20,000
<b>Common Code</b>	MVR400/U
<b>ANSI Ballast</b>	M59
<b>Fixt Rqmt</b>	Enclosed
<b>Burning Position</b>	Universal
<b>Special Desc</b>	Probe Start
<b>Coating</b>	Clear

watch > like > follow



selection. solutions. simplicity. [eiko.com](http://eiko.com)

23220 W. 84<sup>th</sup> St, Shawnee, KS 66227 · (P) 1.800.852.2217 (F) 1.800.492.8975  
 Canada: 81 King St, Barrie, ON L4N 6B5 · (P) 1.888.410.8151 (F) 1.888.705.1335



**Description** 400W ED-37 Mogul Base Universal Burn  
**Ordering Code** 49197  
**UNSPSC Code** 39101614

## Specifications

<b>Watts</b>	400
<b>Base Type</b>	Mogul Screw (E39)
<b>Bulb Type</b>	ED-37
<b>MOL in/mm</b>	11.5/292.1
<b>MOD in/mm</b>	4.65/118.0
<b>LCL in/mm</b>	7.00/178.0
<b>Approx Initial Lumens</b>	36000
<b>Approx Mean Lumens</b>	23000
<b>CT deg K</b>	4000
<b>CRI</b>	70
<b>Rated Life</b>	20,000
<b>Common Code</b>	MVR400/U
<b>ANSI Ballast</b>	M59
<b>Fixt Rqmt</b>	Enclosed
<b>Burning Position</b>	Universal
<b>Special Desc</b>	Probe Start
<b>Coating</b>	Clear

watch > like > follow



selection. solutions. simplicity. [eiko.com](http://eiko.com)

23220 W. 84<sup>th</sup> St, Shawnee, KS 66227 · (P) 1.800.852.2217 (F) 1.800.492.8975  
 Canada: 81 King St, Barrie, ON L4N 6B5 · (P) 1.888.410.8151 (F) 1.888.705.1335