



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



MLTC4HLP316 Coated Metal Locking Tie *Panduit Corporation*

Catalog Number	MLTC4HLP316
Manufacturer	Panduit Corporation
Description	The MLTC4H-LP316 Self-Locking Cable Tie Speeds Up Installation With A Unique Self-Locking Head Design That Locks Into Any Part Of The Tie Body. The Nylon 11 Coating Provides Additional Edge Protection and Prevents Corrosion Between Dissimilar Metals. The 316 Stainless Steel Is Wrapped In Uv-Resistant, Halogen-Free, Low-Smoke Nylon to Promote Worker Safety and Reliability In Corrosive Environments.
Weight per unit	0.9100 (lbs/each)
Product Category	Cable Ties & Wraps

Features

media	Yes
Tensile Strength	250

Dimensions and Weight

Length	14.3
--------	------

Descriptions

Description	COATED METAL LOCKING TIE
extra long description	PAN MLTC4H-LP316 Pan-Steel® MLTC4H-
Long Description	The MLTC4H-LP316 self-locking cable tie speeds up installation with a unique self-locking head design that locks into any part of the tie body. The Nylon 11 coating provides additional edge protection and prevents corrosion between dissimilar metals. The 316 stainless steel is wrapped in UV-resistant, halogen-free, low-smoke Nylon to promote worker safety and reliability in corrosive environments.
Product Type	Pan-Steel® MLTC4H-LP316 Cable Tie, Pa 11 Coated SS 316, Blac
Special Features	Harsh

Manufacturer Information

Brand	PANDUIT
GTIN	00074983221288
Manufacturers Part Number	MLTC4H-LP316
UPC	074983221288



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Screws, Bolts, Staples, Jack Chains, Washers & TY-Raps
Type	Cable Tie

Packaging

Carton	1
Package	50
Weight Per each	0.91

Uses, Certifications, and Standards

Application	Harsh Environment
standard	UL E56854,CE,ABS