



SINGLE AND TWO GANG FLAT COVERS

Single Gang Flat Covers
Horizontal/Vertical 16-in-1

C06



Catalog #: MM110W

APPLICATIONS

Designed for use whenever weatherproof protection is required while an outlet is in use.
N/A

PRODUCT FEATURES

High-impact polycarbonate construction provides maximum durability
Patented Quick-Fit™ keyhole mounting system allows installation in under a minute.
Includes attached gasket and mounting hardware
Pre-configured for GFCI with patented Knockout technology for alternate devices
Lockable tab

UL LISTED

File E116141

NEMA

3R Rated

NEC

2014 Compliant (article 406.9A)

GENERAL PRODUCT INFORMATION

Color: White
Country of Origin: USA

CONFIGURATION

Gangs: 1

PRODUCT MEASUREMENTS

Depth: 5/8 in.
Wt. Ea. (Lbs.): 0.330

PACKAGING

Package Type: Shrink
Std. Pkg.: 10
Product UPC-A Labeled: Yes
Weight (Lbs. Per/C): 33.00
Ship Carton Length (in.): 16.00
Ship Carton Width (in.): 4.38
Ship Carton Height (in.): 6.13
Ctn Weight (Lbs.): 3.30
Pallet Qty: 1890.00
UPC Number: 092326100618
I2of5: 40092326100616