



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



MMX11AA2D8N00 M-Max 1P 115V In/3P 230V Out 2.8A 0.75HP FS2 W/O E Eaton Corp

Catalog Number	MMX11AA2D8N00
Manufacturer	Eaton Corp
Description	Eaton M-Max Series Adjustable Frequency Ac Drives Basic Controller, Full Version, AA Software Design Series, FS2 Frame, 100-120V, 230V, IP20 Enclosure Rating, 0.75 HP, 2.8A Output, 12.4A Input, Single-Phase In, Three-Phase Out
Weight per unit	3.0 (lbs/each)
Product Category	Ac Drives

Features

dimensions	3.5400 IN X 7.6800 IN X 4.0000 IN
Output Current	2.8 A

Descriptions

Description	M-MAX 1P 115V IN/3P 230V OUT 2.8A 0.75HP FS2 W/O E
extra long description	ETN MMX11AA2D8N0-0 MMX 115V/230V 3
Features	Demand more simplicity. The M-Max series of variable frequency drive is a compact system with a broad power range. Factor in the conformal board coating, unique mounting characteristics, simple programming, and its 50°C Rating and the M-Max is perfectly suited for machinery applications in many industries including material handling, HVAC, pumping and more.
Long Description	Eaton M-Max Series Adjustable Frequency AC Drives Basic Controller, Full version, AA software design series, FS2 frame, 100-120V, 230V, IP20 enclosure rating, 0.75 hp, 2.8A output, 12.4A input, Single-phase in, three-phase out
Product Type	MMX 115V/230V 3P, 2.8A, .75HP, FS2, W/O Emc
Special Features	AA software design series

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00786685268460
Manufacturers Part Number	MMX11AA2D8N0-0
UPC	786685268460

Taxonomies, Classifications, and Categories

Category Description	DRIVES
Type	Sensorless vector adjustable frequency drive

Packaging

Carton	1
Weight Per each	3



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

OtherElec Assemblies, Panels & OEM - Electrical Assemblies and
OEMs - Other

standard

EN 60204-1,EN 61800-3,cUL Certified,EN 61800-5-1,UL Listed,CE
Marked,C-Tick Compliant,EMC Category C2, C3, and C4 (Level H):
With an internal RFI filter option,RoHS Compliant