



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



MP350400CPSBU0NL 350/400W BT37 PS Metal Halide EX39 Base

Sylvania-Ledvance

Catalog Number	MP350400CPSBU0NL
Manufacturer	Sylvania-Ledvance
Description	OBS64770 Dual Wattage 350/400W Metalarc Pro Tech Pulse Start Quartz Metal Halide Lamp, Reduced Color Shift, EX39 Base, BT37 Bulb, Open Fixture Rated, Coated, Base Up Only
Weight per unit	1.2 (lbs/each)
Product Category	Lighting

Features

average life	20000
Base	EX39 Exclusionary Mogul
Lamp Type	MP350/400/C/PS/BU-ONLY
lumens	32000
Shape	BT37
Voltage Rating	135
Wattage	350

Material, Color, and Finish

color rendering index (cri)	70
color temperature	3500
Finish	Clear

Dimensions and Weight

Size	11.5
------	------

Descriptions

Description	350/400W BT37 PS METAL HALIDE EX39 BASE
extra long description	SYL MP350/400/C/PS/BU-ONLY/64770 MP
Long Description	OBS64770 Dual wattage 350/400W METALARC PRO TECH PULSE START quartz metal halide lamp, reduced color shift, EX39 base, BT37 bulb, open fixture rated, coated, base up only
Product Type	MP350400CPSBUONLY 6/CS 1/Sku

Manufacturer Information

Brand	LEDVANCE LTD./LTEE.
GTIN	00046135647703
Manufacturers Part Number	MP350/400/C/PS/BU-ONLY/64770
UPC	046135647703

Taxonomies, Classifications, and Categories

Category Description	METAL HALIDE
Type	High Intensity Discharge (HID)



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	1.1833

Uses, Certifications, and Standards

standard	M131/O:M155/O
----------	---------------