



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## MPR1000VBUH00 1000W or MH Mog Base Base Up Burn Pos Lamp

*Ge By Current Lamps*

Catalog Number	MPR1000VBUH00
Manufacturer	Ge By Current Lamps
Description	Metal Halide Lamp, 65, 3500 K, 107000 LM Brightness (Lumens), 1000 W, Clear, Hard Glass Material, 12000 H Average Life, Mogul Base, M47 Ansi Ballast Code, Non Dimmable, 7 In Diameter, 15.37 In Height, 144.9 % Mercury Content, 10.35 LB
Weight per unit	1.7 (lbs/each)
Product Category	Hid Quartz Metal Halide Lamps

### Features

Base	Mogul Screw (EX39)
lumens	110000.0

### Material, Color, and Finish

Color	Clear
color rendering index (cri)	65.0
Finish	Clear
Style	Open or enclosed fixtures

### Descriptions

Description	1000W OR MH MOG BASE BASE UP BURN POS LAMP
extra long description	GEL MPR1000/VBU/HO/O 41433 MULTIVAP
Special Features	15.37IN Length

### Manufacturer Information

Brand	Ge Traditional Lamps
GTIN	00043168414333
UPC	043168414333

### Taxonomies, Classifications, and Categories

Category Description	METAL HALIDE
----------------------	--------------

### Packaging

Carton	1
Package	6
Weight Per each	1.73