



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## MS750PSBUHORBT37 750W MH Pulse Start Lamp

*Sylvania-Ledvance*

Catalog Number	MS750PSBUHORBT37
Manufacturer	Sylvania-Ledvance
Description	750W Metalarc Pulse Start Quartz Metal Halide Lamp, High Output, Position Dedicated, Reduced Color Shift, E39 Base, BT37 Bulb, Enclosed Fixture Rated, Base Up Through Horizontal, Clear, 4000K
Weight per unit	1.2 (lbs/each)
Product Category	Hid Quartz Metal Halide Lamps

### Features

average life	12000
Base	E39 Mogul
lumens	78000
Shape	BT37
Voltage Rating	200
Wattage	750

### Material, Color, and Finish

color rendering index (cri)	65
color temperature	4000
Finish	Clear

### Dimensions and Weight

Size	11.5
------	------

### Descriptions

Description	750W MH PULSE START LAMP
extra long description	SYL MS750/PS/BU-HOR/BT37/64787 MS75
Long Description	750W METALARC PULSE START quartz metal halide lamp, high output, position dedicated, reduced color shift, E39 base, BT37 bulb, enclosed fixture rated, base up through horizontal, clear, 4000K
Product Type	MS750PSBUHORBT37 6/CS 1/Sku

### Manufacturer Information

Brand	SYLVANIA
GTIN	00046135647871
Manufacturers Part Number	MS750/PS/BU-HOR/BT37/64787
UPC	046135647871

### Taxonomies, Classifications, and Categories

Category Description	METAL HALIDE
Type	High Intensity Discharge (HID)



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Package	6
Weight Per each	1.18

## Uses, Certifications, and Standards

standard	M149/E
----------	--------