



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## MVR1000UBT37 1000W BT37 Metal Halide Reduced Glass Clear Mogul

*Ge By Current Lamps*

Catalog Number	MVR1000UBT37
Manufacturer	Ge By Current Lamps
Description	Metal Halide Lamp, 65, 3700 K, 105000 LM (Horizontal);115000 LM (Vertical) Brightness (Lumens), 1000 W, Clear, Hard Glass Material, 9000 H (Horizontal);12000 H (Vertical) Average Life, Mogul Base, M47 Ansi Ballast Code, Non Dimmable, 4.625 In Diameter, 11.5 In Height, 150 % Mercury Content, 4.45 LB
Weight per unit	0.7400 (lbs/each)
Product Category	Hid Quartz Metal Halide Lamps

### Features

Base	Mogul Screw (E39)
------	-------------------

### Material, Color, and Finish

Color	Clear
color rendering index (cri)	65.0
Finish	Clear
Style	Enclosed fixtures only

### Descriptions

Description	1000W BT37 METAL HALIDE REDUCED GLASS CLEAR MOGUL
extra long description	GEL MVR1000/U/BT37 18205 MULTIVAPOR
Special Features	11.5IN Length

### Manufacturer Information

Brand	Ge Traditional Lamps
GTIN	00043168182058
UPC	043168182058

### Taxonomies, Classifications, and Categories

Category Description	METAL HALIDE
----------------------	--------------

### Packaging

Carton	1
Package	6
Weight Per each	0.74

### Uses, Certifications, and Standards

Application	Universal burning position
-------------	----------------------------