



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



MVR150UMED 150W BD17 Metal Halide Clear Medium Base Lamp

Ge By Current Lamps

Catalog Number	MVR150UMED
Manufacturer	Ge By Current Lamps
Description	Metal Halide Lamp, 65, 4300 K, 14000 LM Brightness (Lumens), 150 W, Clear, Hard Glass Material, 15000 H Average Life, Medium Base, M102 Ansi Ballast Code, Non Dimmable, 2.125 In Diameter, 5.43 In Height, 10.8 % Mercury Content, 1.78 LB
Weight per unit	0.3000 (lbs/each)
Product Category	Hid Quartz Metal Halide Lamps

Features

Base	Medium Screw (E26)
lumens	14000.0
Wattage	150.0

Material, Color, and Finish

Color	Clear
color rendering index (cri)	65.0
Style	Enclosed fixtures only

Descriptions

Description	150W BD17 METAL HALIDE CLEAR MEDIUM BASE LAMP
extra long description	GEL MVR150/U/MED 12598 MULTIVAPOR
Special Features	5.43IN Length

Manufacturer Information

Brand	Ge Traditional Lamps
GTIN	00043168125987
UPC	043168125987

Taxonomies, Classifications, and Categories

Category Description	METAL HALIDE
----------------------	--------------

Packaging

Carton	1
Package	6
Weight Per each	0.3

Uses, Certifications, and Standards

Application	Universal burning position
-------------	----------------------------