



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



MVR175UMED 175W BD17 Metal Halide Clear Medium Base Lamp

Ge By Current Lamps

Catalog Number	MVR175UMED
Manufacturer	Ge By Current Lamps
Description	Metal Halide Lamp, 65, 4000 K, 11700 LM (Horizontal);13600 LM (Vertical) Brightness (Lumens), 175 W, Clear, Hard Glass Material, 6000 H (Horizontal);10000 H (Vertical) Average Life, Medium Base, M57 Ansi Ballast Code, Non Dimmable, 2.12 In Diameter, 5.75 In Height, 25.74 % Mercury Content, 1.22 LB
Weight per unit	0.2200 (lbs/each)
Product Category	Hid Quartz Metal Halide Lamps

Features

Base	Medium Screw (E26)
Wattage	175.0

Material, Color, and Finish

Color	Clear
color rendering index (cri)	65.0
Style	Enclosed fixtures only

Descriptions

Description	175W BD17 METAL HALIDE CLEAR MEDIUM BASE LAMP
extra long description	GEL MVR175/U/MED 18902 MULTIVAPOR
Special Features	5.75IN Length

Manufacturer Information

Brand	Ge Traditional Lamps
GTIN	00043168189026
UPC	043168189026

Taxonomies, Classifications, and Categories

Category Description	METAL HALIDE
----------------------	--------------

Packaging

Carton	1
Package	6
Weight Per each	0.22