



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## MVR250U 250W ED28 Metal Halide Clear Mogul Base Lamp

*Ge By Current Lamps*

|                  |   |
|------------------|---|
| Catalog Number   | MVR250U   |
| Manufacturer     | Ge By Current Lamps   |
| Description      | Metal Halide Lamp, 65, 4200 K, 19100 LM (Horizontal);20800 LM (Vertical) Brightness (Lumens), 250 W, Clear, Hard Glass Material, 6000 H (Horizontal);10000 H (Vertical) Average Life, Mogul Base, M58 Ansi Ballast Code, Non Dimmable, 3.5 In Diameter, 8.25 In Height, 31 % Mercury Content, 5.55 LB |
| Weight per unit  | 0.4600 (lbs/each)   |
| Product Category | Hid Quartz Metal Halide Lamps   |

### Features

|         |                   |
|---------|-------------------|
| Base    | Mogul Screw (E39) |
| Wattage | 250.0             |

### Material, Color, and Finish

|                             |                        |
|-----------------------------|------------------------|
| Color                       | Clear                  |
| color rendering index (cri) | 65.0                   |
| Style                       | Enclosed fixtures only |

### Descriptions

|                        |  |
|------------------------|--|
| Description            | 250W ED28 METAL HALIDE CLEAR MOGUL BASE LAMP |
| extra long description | GEL MVR250/U 42729 MULTIVAPOR                |
| Special Features       | 8.25IN Length                                |

### Manufacturer Information

|       |                      |
|-------|----------------------|
| Brand | Ge Traditional Lamps |
| GTIN  | 00043168427296       |
| UPC   | 043168427296         |

### Taxonomies, Classifications, and Categories

|                      |              |
|----------------------|--------------|
| Category Description | METAL HALIDE |
|----------------------|--------------|

### Packaging

|                 |      |
|-----------------|------|
| Carton          | 1    |
| Package         | 12   |
| Weight Per each | 0.46 |

### Uses, Certifications, and Standards

|             |                            |
|-------------|----------------------------|
| Application | Universal burning position |
|-------------|----------------------------|