



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



MVR320VBUH0PA 320W ED28 Metal Halide Clear Mogul Base Pulserc

Ge By Current Lamps

Catalog Number	MVR320VBUH0PA
Manufacturer	Ge By Current Lamps
Description	Metal Halide Lamp, 65, 4000 K, 31000 LM Brightness (Lumens), 320 W, Clear, Hard Glass Material, 20000 H Average Life, Mogul Base, M132/M154 Ansi Ballast Code, Non Dimmable, 3.5 In Diameter, 8.25 In Height, 30 % Mercury Content, 5.33 LB
Weight per unit	0.4600 (lbs/each)
Product Category	Hid Quartz Metal Halide Lamps

Features

Base	Mogul Screw (E39)
lumens	31000.0
Wattage	320.0

Material, Color, and Finish

Color	Clear
color rendering index (cri)	65.0
Finish	Clear
Style	Enclosed fixtures only

Descriptions

Description	320W ED28 METAL HALIDE CLEAR MOGUL BASE PULSERC
extra long description	GEL MVR320/VBU/HO/PA 27501 MULTIVAP
Special Features	8.25IN Length

Manufacturer Information

Brand	Ge Traditional Lamps
GTIN	00043168275019
UPC	043168275019

Taxonomies, Classifications, and Categories

Category Description	METAL HALIDE
----------------------	--------------

Packaging

Carton	1
Package	12
Weight Per each	0.46

Uses, Certifications, and Standards

Application	Vertical base up +/-15°
-------------	-------------------------