



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## MVR320VBUH0PA 320W ED28 Metal Halide Clear Mogul Base Pulserc

*Ge By Current Lamps*

|                  |   |
|------------------|---|
| Catalog Number   | MVR320VBUH0PA   |
| Manufacturer     | Ge By Current Lamps   |
| Description      | Metal Halide Lamp, 65, 4000 K, 31000 LM Brightness (Lumens), 320 W, Clear, Hard Glass Material, 20000 H Average Life, Mogul Base, M132/M154 Ansi Ballast Code, Non Dimmable, 3.5 In Diameter, 8.25 In Height, 30 % Mercury Content, 5.33 LB |
| Weight per unit  | 0.4600 (lbs/each)   |
| Product Category | Hid Quartz Metal Halide Lamps   |

### Features

|         |                   |
|---------|-------------------|
| Base    | Mogul Screw (E39) |
| lumens  | 31000.0           |
| Wattage | 320.0             |

### Material, Color, and Finish

|                             |                        |
|-----------------------------|------------------------|
| Color                       | Clear                  |
| color rendering index (cri) | 65.0                   |
| Finish                      | Clear                  |
| Style                       | Enclosed fixtures only |

### Descriptions

|                        |   |
|------------------------|---|
| Description            | 320W ED28 METAL HALIDE CLEAR MOGUL BASE PULSERC |
| extra long description | GEL MVR320/VBU/HO/PA 27501 MULTIVAP             |
| Special Features       | 8.25IN Length                                   |

### Manufacturer Information

|       |                      |
|-------|----------------------|
| Brand | Ge Traditional Lamps |
| GTIN  | 00043168275019       |
| UPC   | 043168275019         |

### Taxonomies, Classifications, and Categories

|                      |              |
|----------------------|--------------|
| Category Description | METAL HALIDE |
|----------------------|--------------|

### Packaging

|                 |      |
|-----------------|------|
| Carton          | 1    |
| Package         | 12   |
| Weight Per each | 0.46 |

### Uses, Certifications, and Standards

|             |                         |
|-------------|-------------------------|
| Application | Vertical base up +/-15° |
|-------------|-------------------------|