



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



MVR400CU *Delisted* 400W ED37 MH Coated Mogul Base Lamp

Ge By Current Lamps

Catalog Number	MVR400CU
Manufacturer	Ge By Current Lamps
Description	Ge Multi-Vapor®, 43829, 400 WTT, 3700 KV, 70 Cri, Mogul Screw (E39) Base
Weight per unit	0.7400 (lbs/each)
Product Category	Hid Quartz Metal Halide Lamps

Features

Base	Mogul Screw (E39)
Wattage	400.0

Material, Color, and Finish

Color	COATED
color rendering index (cri)	70.0
color temperature	3700.0
Finish	COATED
Style	Open Fixture-Restricted Position (S-Rated)

Descriptions

Description	*DELISTED* 400W ED37 MH COATED MOGUL BASE LAMP
extra long description	GEL MVR400/C/U 43829 MULTIVAPOR
Long Description	GE Multi-Vapor®, 43829, 400 WTT, 3700 KV, 70 CRI, Mogul Screw (E39) Base
Product Type	43829 Multivapor
Special Features	11.5IN Length

Manufacturer Information

Brand	GE Current
GTIN	00043168438292
Manufacturers Part Number	MVR400/C/U
UPC	043168438292

Taxonomies, Classifications, and Categories

Category Description	METAL HALIDE
----------------------	--------------

Packaging

Carton	1
Package	6
Weight Per each	0.74

Uses, Certifications, and Standards

Application	Universal burning position
-------------	----------------------------