



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1904 Dutton Drive
78666-0000, TX San Marcos
Phone: 512-392-4310
Fax: 512-392-4390



MXR150UMEDO 150W or PS/MH Med Screw Universal Burn Position

Ge By Current Lamps

Catalog Number	MXR150UMEDO
Manufacturer	Ge By Current Lamps
Description	Metal Halide Lamp, 70, 3500 K, 12500 LM Brightness (Lumens), 150 W, Clear, Hard Glass Material, 15000 H Average Life, Medium Base, M102 Ansi Ballast Code, Non Dimmable, 2.125 In Diameter, 5.43 In Height, 11.4 % Mercury Content, 1.78 LB
Weight per unit	0.3000 (lbs/each)
Product Category	Hid Quartz Metal Halide Lamps

Features

Base	Medium Screw (E26)
lumens	12500
Wattage	150

Material, Color, and Finish

Color	Clear
color rendering index (cri)	70
Finish	Clear
Style	Open or enclosed fixtures

Descriptions

Description	150W OR PS/MH MED SCREW UNIVERSAL BURN POSITION
extra long description	GEL MXR150/U/MED/O 45683 MULTIVAPOR
Special Features	5.43IN Length

Manufacturer Information

Brand	Ge Traditional Lamps
GTIN	00043168456838
Manufacturers Part Number	MXR150/U/MED/O
UPC	043168456838

Taxonomies, Classifications, and Categories

Category Description	METAL HALIDE
----------------------	--------------

Packaging

Carton	1
Package	6
Weight Per each	0.3

Uses, Certifications, and Standards

Application	Universal burning position
-------------	----------------------------