

Eaton NON-100

Catalog Number: NON-100

Eaton Bussmann series NON fuse, Non current limiting, Light duty circuit locations, 100 A, Class H, Non-indicating, Blade end x blade end, 50 kAIC at 125 Vdc|10 kAIC at 250 Vac, Standard, 5, 250 V, 125 Vdc

General specifications

Product Name	Catalog Number
Eaton Bussmann series NON fuse	NON-100
UPC	EAN
051712101684	5027590065283
Product Length/Depth	Product Height
1.125 in	5.875 in
Product Width	Product Weight
1.125 in	0.278 lb
Warranty	Compliances
Not Applicable	CE Marked



Electrical rating

Amperage Rating

100 A

Interrupt rating

10 kAIC at 250 Vac

50 kAIC at 125 Vdc

Voltage rating

250 Vac, 125 Vdc

Physical details

Packaging type

Standard

General information

Class

Class H

Connection

Blade end x blade end

Fuse indicator

Non-indicating

Quantity

5

Special features

Non current limiting

Resources

Catalogs

[Bussmann series complete full line catalog no. 1007](#)

[Bussmann series full line catalog 1007, section 01- low voltage branch circuit fuses](#)

Multimedia

[Bussmann series Fuseology](#)

Specifications and datasheets

[Eaton Specification Sheet - NON-100](#)

Technical data sheets

[NON-100~BUSS ONE TIME FUSE](#)

Technical service bulletins

[Datasheet - FNQ-30](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)