

Eaton NON-30

Catalog Number: NON-30

Eaton Bussmann series NON fuse, Non current limiting, Light duty circuit locations, 30 A, Class H, Non-indicating, Ferrule end x ferrule end, 50 kAIC at 250 Vac|50 kAIC at 125 Vdc, Standard, 10, 250 V, 125 Vdc

General specifications



Product Name	Catalog Number
Eaton Bussmann series NON fuse	NON-30
UPC	Product Length/Depth
051712101592	2 in
Product Height	Product Width
0.56 in	0.56 in
Product Weight	Warranty
0.036 lb	Not Applicable
Compliances	
CE Marked	

Electrical rating

Amperage Rating

30 A

Interrupt rating

50 kAIC at 125 Vdc

50 kAIC at 250 Vac

Voltage rating

250 Vac, 125 Vdc

Physical details

Packaging type

Standard

General information

Class

Class H

Connection

Ferrule end x ferrule end

Fuse indicator

Non-indicating

Quantity

10

Special features

Non current limiting

Resources

Catalogs

[Bussmann series full line catalog 1007, section 01- low voltage branch circuit fuses](#)

[Bussmann series complete full line catalog no. 1007](#)

Multimedia

[Bussmann series Fuseology](#)

Specifications and datasheets

[Eaton Specification Sheet - NON-30](#)

Technical data sheets

[NON-30~BUSS ONE TIME FUSE](#)

Technical service bulletins

[Datasheet - FNQ-30](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)