

Eaton NOS-30

Catalog Number: NOS-30

Eaton Bussmann series NOS fuse, Non current limiting, Light duty circuit locations, 30 A, Class H, Non-indicating, Ferrule end x ferrule end, 50 kAIC at 600 Vac, Standard, 10, 600 V

General specifications

Product Name	Catalog Number
Eaton Bussmann series NOS fuse	NOS-30
UPC	Product Length/Depth
051712310307	5 in
Product Height	Product Width
0.81 in	0.81 in
Product Weight	Warranty
0.153 lb	Not Applicable
Compliances	
CE Marked	



Electrical rating

Amperage Rating

30 A

Interrupt rating

50 kAIC at 600 Vac

Voltage rating

600 V

Physical details

Packaging type

Standard

General information

Class

Class H

Connection

Ferrule end x ferrule end

Fuse indicator

Non-indicating

Quantity

10

Special features

Pin-indicating

Resources

Catalogs

Bussmann series complete full line catalog no. 1007

Multimedia

Bussmann series Fuseology

Specifications and datasheets

Eaton Specification Sheet - NOS-30

Technical data sheets

NOS-30-BUSS ONE TIME FUSE

Technical service bulletins

Datasheet - FNQ-30



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)