



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## N350 350 Cu Split Bolt

*Nsi Industries*

Catalog Number	N350
Manufacturer	Nsi Industries
Description	Copper Split Bolt Connector 350 MCM Copper Split Bolt Connectors Are High-Strength Solderless Service Connectors Made Of High-Copper Alloy For Copper and Copperweld Wires. Type For Two Maximum Wire Sizes.
Weight per unit	0.8300 (lbs/each)
Product Category	Large Terminals & Connectors

### Features

Material	Copper
Number of Conductors	2
Poles	1
Voltage Rating	600 V
Warranty	1 YEAR
Wire Size	4/0 STR - 350 MCM
Wire Type	Class A & B

### Material, Color, and Finish

Color	Copper
Finish	COPPER

### Dimensions and Weight

Size	L=2.440 - W=1.220
------	-------------------

### Descriptions

Description	350 CU SPLIT BOLT
extra long description	NSI N-350 Split Bolt Copper 350
Features	Copper Split Bolt Connector 350 MCM Copper Split Bolt Connectors are high-strength solderless service connectors made of high-copper alloy for copper and copperweld wires. Type for two maximum wire sizes.
Long Description	Copper Split Bolt Connector 350 MCM Copper Split Bolt Connectors are high-strength solderless service connectors made of high-copper alloy for copper and copperweld wires. Type for two maximum wire sizes.
Product Type	Split Bolt Copper 350
Special Features	4/0 STR-350 MCM - 4 Pack



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	NSi
GTIN	00662381020109
Manufacturers Part Number	N-350
UPC	662381020109

## Taxonomies, Classifications, and Categories

Category Description	SPLIT BOLTS
Type	Copper Split Bolts

## Packaging

Carton	1
Package	4
Weight Per each	0.83

## Uses, Certifications, and Standards

Application	Wire Termination
environmental conditions	90 C
standard	UL486B
Temperature Rating	90 C