


## All Purpose Type Split Bolts - N-500SP



Drawn - SD

Approved - KM

Material - Copper / Finish: Tin Plated

Title - All Purpose Type Split Bolts



Max Run To Max Tap		500 - 500 STR AL-CU
Min Run To Min Tap		400 - 2/0 STR AL-CU
Max Run To Min Tap		500 - 2/0 STR AL-CU
Min Equal Run - Tap		300 - 300 STR AL-CU
4	Spacer	Electrolytical Copper
3	Nut	Bronze
2	Rider	Bronze
1	Body	Electrolytical Copper

