

# Eaton NCG50 50

Catalog Number: NCG50 50

Eaton Crouse-Hinds series NCG cord grip, Cable range min/max: 0.20-0.50", Non-armoured and tray cable, Non-armoured gland, Polyamide 6, General purpose, 1/2" NPT



## General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series NCG cord grip	NCG50 50
	UPC
	784564002440
Product Length/Depth	Product Height
0.5 in	2.38 in
Product Width	Product Weight
0.5 in	0.02 lb

## Certifications and compliances

### Area classification

Ordinary/Non-Hazardous Locations

### Standards type

NEC/CEC

### NEMA Rating

4X

### Ingress protection (IP) ratings

IP68

## Product specifications

### Protection type

General purpose

### Cable type

Tray cable

Non-armoured

### Gland type

Non-armoured

### Thread Size

1/2"

### Thread type

NPT

### Cable range (min/max)

0.20-0.50"

### Material

Polyamide 6

## Resources

### Catalogs

[Crouse-Hinds series NCG and NCGB catalog page](#)

### Certification reports

[NCG, NCGB and NCGS Non-metallic Portable Cord Connectors Canadian certification](#)

[NCG, NCGB and NCGS Non-metallic Portable Cord Connectors UL certification](#)

### Specifications and datasheets

[Eaton Specification Sheet - NCG50 50](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)