



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



NFFLDC40T Trun 128W Led Flood 40K

Cooper Lighting Solutions

Catalog Number	NFFLDC40T
Manufacturer	Cooper Lighting Solutions
Description	Led Flood Light, Die-Cast Aluminum, 120 to 277 V Ac;347 V Ac;480 V Ac, 128 W, 70, 16900 LM Brightness (Lumens), 4000 K, Powder Coat, 15-15/16 In Length, 8-11/16 In Width, 12-11/16 In Height, Tempered Glass Lens Material, Trunion Mount, +40 °C Operating Temperature, -40 °C Operating Temperature, 60000 H Average Life, 5 Yr Warranty, 20 LB
Weight per unit	22.9 (lbs/each)
Product Category	Led Floodlights

Features

amperage rating	0.466 (at 277V)
Ballast Type	N/A
battery	N/A
Fixture Type	FLOODLIGHT
Lamp Type	LED
lumens	16,932
media	Yes
Number of Lamps	2
Shape	Rectangular

Dimensions and Weight

Size	18.0 IN Length 7.5 IN Width 9.5 IN Height
------	-------------------------------------------

Descriptions

Description	TRUN 128W LED FLOOD 40K
extra long description	CLS NFFLD-C40-T NFFLD,129W,4000K,UN
Special Features	Die-cast aluminum housing, driver compartment and driver door

Manufacturer Information

Brand	LUMARK
GTIN	00080083801183
UPC	080083801183

Taxonomies, Classifications, and Categories

Category Description	LED FLOODLIGHTS, WALLPACKS, BOLLARDS & LANDSCAPE LIGHTING
Type	FLOODLIGHT

Packaging

Carton	1
Weight Per each	22.85



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Mounting

TRUNNION

standard

UL/cUL Listed - Wet Location;RoHS Compliant